


## 7. UNDERCARRIAGE

### 1) TRACKS

X-leg type center frame is integrally welded with reinforced box-section track frames. The design includes dry tracks, lubricated rollers, idlers, sprockets, hydraulic track adjusters with shock absorbing springs and assembled track-type tractor shoes with triple grousers.

### 2) TYPES OF SHOES

Model	Shapes		Triple grouser		
					
R145CR-9	Shoe width	mm (in)	※ 500 (20)	600 (24)	700 (28)
	Operating weight	kg (lb)	14600/32190	14790 (32610)	15020 (33110)
	Ground pressure	kgf/cm <sup>2</sup> (psi)	0.46 (6.54)	0.39 (5.55)	0.34 (4.83)
	Overall width	mm (ft-in)	2500 (8' 2")	2600 (8' 6")	2700 (8' 10")
R145CRD-9	Shoe width	mm (in)	※ 500 (20)	600 (24)	700 (28)
	Operating weight	kg (lb)	15400 (33950)	15610 (34610)	15840 (34920)
	Ground pressure	kgf/cm <sup>2</sup> (psi)	0.49 (6.97)	0.41 (5.83)	0.36 (5.12)
	Overall width	mm (ft-in)	2500 (8' 2")	2600 (8' 6")	2700 (8' 10")
R145LCR-9	Shoe width	mm (in)	※ 500 (20)	600 (24)	700 (28)
	Operating weight	kg (lb)	14660 (32320)	14850 (32740)	15080 (33250)
	Ground pressure	kgf/cm <sup>2</sup> (psi)	0.47 (6.68)	0.39 (5.55)	0.34 (4.83)
	Overall width	mm (ft-in)	2500 (8' 2")	2600 (8' 6")	2700 (8' 10")

※ : Standard

### 3) NUMBER OF ROLLERS AND SHOES ON EACH SIDE

Item	Quantity	
	R145CR-9/R145CRD-9	R145LCR-9
Carrier rollers	1 EA	1 EA
Track rollers	7 EA	7 EA
Track shoes	45 EA	46 EA

#### 4) SELECTION OF TRACK SHOE

Suitable track shoes should be selected according to operating conditions.

##### Method of selecting shoes

Confirm the category from the list of applications in **table 2**, then use **table 1** to select the shoe. Wide shoes (Categories B and C) have limitations on applications. Before using wide shoes, check the precautions, then investigate and study the operating conditions to confirm if these shoes are suitable.

Select the narrowest shoe possible to meet the required flotation and ground pressure. Application of wider shoes than recommendations will cause unexpected problem such as bending of shoes, crack of link, breakage of pin, loosening of shoe bolts and the other various problems.

※ **Table 1**

Track shoe	Specification	Category
500 mm triple grouser	Standard	A
600 mm triple grouser	Option	A
700 mm triple grouser	Option	B

※ **Table 2**

Category	Applications	Applications
A	Rocky ground, river beds, normal soil	<ul style="list-style-type: none"> <li>• Travel at low speed on rough ground with large obstacles such as boulders or fallen trees</li> </ul>
B	Normal soil, soft ground	<ul style="list-style-type: none"> <li>• These shoes cannot be used on rough ground with large obstacles such as boulders or fallen trees</li> <li>• Travel at high speed only on flat ground</li> <li>• Travel slowly at low speed if it is impossible to avoid going over obstacles</li> </ul>